



SPN215R

**SPD 2P pluggable 15kA class 2 with reserve + remote contact**

**Technical characteristics**

**Architecture**

Type of pole	1P+N
--------------	------

**Controls and indicators**

Indicator lamp	reserve
----------------	---------

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

**Electric current**

Max discharge (Imax) L-N(PEN)/ N-PE	15 kA
-------------------------------------	-------

**Dimensions**

Width of installed product	36 mm
----------------------------	-------

**Power**

Total power loss under IN	0 W
---------------------------	-----

**Installation, mounting**

Tightening torque	3,6Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	25mm <sup>2</sup>
Connection cross-sect. rigid cable	35mm <sup>2</sup>

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Use conditions**

Operating temperature	-40...55 °C
-----------------------	-------------