



SPN240R

SPD 2P pluggable 40kA class 2 with reserve + remote contact

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

Dimensions

Width of installed product	36 mm
----------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------