



SPN240R

SPD 2P pluggable 40kA class 2 with reserve + remote contact

Technical characteristics

Controls and indicators

Indicator lamp	reserve
----------------	---------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	40 kA
--	-------

Dimensions

Width of installed product	36 mm
----------------------------	-------

Power

Total power loss under I _N	0 W
---------------------------------------	-----

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------