



SPN265R

**SPD 2P pluggable 65kA class 2 with reserve + remote contact**

**Technical Characteristics**

|   |                   |
|---|-------------------|
| Type of pole                              | 1P+N              |
| Indicator lamp                            | reserve           |
| With remote signalling contact            | Yes               |
| Rated operational voltage Ue              | 230 V             |
| Frequency                                 | 50/60 Hz          |
| Max discharge (Imax) L-N(PEN)/ N-PE       | 65 kA             |
| Width of installed product                | 36 mm             |
| Total power loss under IN                 | 0 W               |
| Number of modules                         | 2                 |
| Tightening torque                         | 3,6Nm             |
| Connection cross-sect. flexible conductor | 25mm <sup>2</sup> |
| Connection cross-sect. rigid cable        | 35mm <sup>2</sup> |
| European directive WEEE                   | concerned         |
| Operating temperature                     | -40...55 °C       |