



SPN265R

## SPD 2P pluggable 65kA class 2 with reserve + remote contact

### Technical characteristics

#### Controls and indicators

Indicator lamp	reserve
----------------	---------

#### Main electrical features

Rated operational voltage $U_e$	230 V
Frequency	50/60 Hz

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	65 kA
--	-------

#### Dimensions

Width of installed product	36 mm
----------------------------	-------

#### Power

Total power loss under $I_N$	0 W
------------------------------	-----

#### Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

#### Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------