



SPN415D

SPD 4P pluggable 15kA class 2 with end of life indicator

Technical Characteristics

Type of pole	3P+N
Indicator lamp	end of life indicator
With remote signalling contact	No
Rated operational voltage Ue	230 / 400 V
Frequency	50/60 Hz
Max discharge (Imax) L-N(PEN)/ N-PE	15 kA
Width of installed product	72 mm
Total power loss under IN	0 W
Number of modules	4
Tightening torque	3,6Nm
Connection cross-sect. flexible conductor	25mm ²
Connection cross-sect. rigid cable	35mm ²
European directive WEEE	concerned
Operating temperature	-40...55 °C