



SPN440D

SPD 4P pluggable 40kA class 2 with end of life indicator

Technical characteristics

Architecture

Type of pole 3P+N

Controls and indicators

Indicator lamp end of life indicator

Main electrical features

Rated operational voltage U_e 230 / 400 V

Frequency 50/60 Hz

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 40 kA

Dimensions

Width of installed product 72 mm

Power

Total power loss under IN 0 W

Installation, mounting

Tightening torque 3,6Nm

Connection

Connection cross-sect. flexible conductor 25mm²

Connection cross-sect. rigid cable 35mm²

Standards

European directive WEEE concerned

Use conditions

Operating temperature -40...55 °C