



SPN440D

## SPD 4P pluggable 40kA class 2 with end of life indicator

### Technical characteristics

#### Architecture

Type of pole 3P+N

#### Controls and indicators

Indicator lamp end of life indicator

#### Main electrical features

Rated operational voltage  $U_e$  230 / 400 V

Frequency 50/60 Hz

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE 40 kA

#### Dimensions

Width of installed product 72 mm

#### Power

Total power loss under IN 0 W

#### Installation, mounting

Tightening torque 3,6Nm

#### Connection

Connection cross-sect. flexible conductor 25mm<sup>2</sup>

Connection cross-sect. rigid cable 35mm<sup>2</sup>

#### Use conditions

Operating temperature -40...55 °C