



SPN440D

SPD 4P pluggable 40kA class 2 with end of life indicator

Technical characteristics

Architecture

Type of pole	3P+N
--------------	------

Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

Dimensions

Width of installed product	72 mm
----------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	25mm ²
Connection cross-sect. rigid cable	35mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------