



SPN440R

## SPD 4P pluggable 40kA class 2 with reserve + remote contact

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50/60 Hz

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

#### Dimensions

Width of installed product	72 mm
----------------------------	-------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------