



SPV025



## Cartridge +/- for SPV325

### Technical characteristics

#### Architecture

Type of pole Phase

#### Controls and indicators

Indicator lamp reserve

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 25 kA

#### Dimensions

Width of installed product 18 mm

#### Power

Total power loss under IN 0 W

#### Use conditions

Operating temperature -40...80 °C