



SPV025

Cartridge +/- for SPV325

Technical characteristics

Architecture

Type of polePhase

Controls and indicators

Indicator lampreserve

Main electrical features

Frequency50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE25 kA

Dimensions

Width of installed product18 mm

Power

Total power loss under IN0 W

Standards

European directive WEEEconcerned

Use conditions

Operating temperature-40...80 °C