



SPV025E

Cartridge earth for SPV325

Technical characteristics

Main electrical features

Frequency 50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 25 kA

Dimensions

Width of installed product 18 mm

Power

Total power loss under IN 0 W

Standards

European directive WEEE concerned

Use conditions

Operating temperature -40...80 °C