



SPV025E

Cartridge earth for SPV325

Technical characteristics

Architecture

Type of pole	PE
--------------	----

Controls and indicators

Indicator lamp	reserve
----------------	---------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	25 kA
--	-------

Dimensions

Width of installed product	18 mm
----------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------