



SPV040

## Cartridge T2 1P photovoltaic +/- for SPV340

### Technical characteristics

#### Controls and indicators

Indicator lamp	Optic
----------------	-------

#### Main electrical features

Rated operational voltage Ue	1000 V
------------------------------	--------

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

#### Dimensions

Depth of installed product	43.4 mm
Height of installed product	52.4 mm
Width of installed product	17.5 mm

#### Installation, mounting

Tightening torque	3
-------------------	---

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------