



SPV040

Cartridge T2 1P photovoltaic +/- for SPV340

Technical characteristics

Controls and indicators

Indicator lamp	Optic
----------------	-------

Main electrical features

Rated operational voltage Ue	1000 V
------------------------------	--------

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

Dimensions

Depth of installed product	43.4 mm
Height of installed product	52.4 mm
Width of installed product	17.5 mm

Installation, mounting

Tightening torque	3
-------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------