



SPV325

## SPD pluggable photovoltaic 25kA class 2

### Technical characteristics

#### Architecture

Type of pole	2 P
--------------	-----

#### Controls and indicators

Indicator lamp	reserve
----------------	---------

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	25 kA
-------------------------------------	-------

#### Dimensions

Width of installed product	54 mm
----------------------------	-------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1,5 / 25mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 35mm <sup>2</sup>

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------