



SPV325

SPD pluggable photovoltaic 25kA class 2

Technical Characteristics

Type of pole	2 P
Indicator lamp	reserve
Frequency	50/60 Hz
Max discharge (I _{max}) L-N(PEN)/ N-PE	25 kA
Width of installed product	54 mm
Total power loss under IN	0 W
Number of modules	3
Tightening torque	3,6Nm
Connection cross-sect. flexible conductor	1,5 / 25mm ²
Connection cross-sect. rigid cable	1,5 / 35mm ²
European directive WEEE	concerned
Operating temperature	-40...80 °C