



SR600

Current transformer 600 / 5A

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	75 mm
Height of installed product	70 mm
Width of installed product	77 mm
Height of opening	40 mm

Power

Total power loss under IN	0 W
---------------------------	-----

Connection

Connection cross-sect. flexible conductor	1,5 / 4mm ²
Connection cross-sect. rigid cable	2,5 / 6mm ²
Type of connection	screw

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...50 °C
-----------------------	-------------