



SRA00505

Bar/Cable-through Current Transformer BG 213 50/5A 1,5VA Class 1

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	3 kV
--------------------------	------

Dimensions

Depth of installed product	30 mm
Height of installed product	78 mm
Width of installed product	60 mm
Height of opening	20 mm

Power

Total power loss under IN	0.5 W
---------------------------	-------

Connection

Type of connection	screw
--------------------	-------

Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------