



SRA01005

**Bar/Cable-through Current Transformer BG 113 100/5A 2,5VA Class 1**

**Technical characteristics**

**Main electrical features**

Frequency 50/60 Hz

**Voltage**

Rated insulation voltage 3 kV

**Dimensions**

Depth of installed product 30 mm

Height of installed product 70 mm

Width of installed product 49.5 mm

Height of opening 20 mm

**Power**

Total power loss under IN 0.7 W

**Connection**

Connection cross-sect. flexible conductor 1,5 / 6mm<sup>2</sup>

Connection cross-sect. rigid cable 1,5 / 6mm<sup>2</sup>

Type of connection screw

**Use conditions**

Operating temperature -40...40 °C