



SRA01505

Bar/Cable-through Current Transformer BG 113 150/5A 2,5VA Class 1

Technical characteristics

Main electrical features

Frequency 50/60 Hz

Voltage

Rated insulation voltage 3 kV

Dimensions

Depth of installed product 30 mm

Height of installed product 70 mm

Width of installed product 49.5 mm

Height of opening 20 mm

Power

Total power loss under IN 1 W

Connection

Type of connection screw

Standards

European directive WEEE concerned

Use conditions

Operating temperature -40...40 °C