



SRA02505

Bar/Cable-through Current Transformer BG 113 250/5A 2,5VA Class 1

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	3 kV
--------------------------	------

Dimensions

Depth of installed product	30 mm
Height of installed product	70 mm
Width of installed product	49.5 mm
Height of opening	20 mm

Power

Total power loss under IN	2.6 W
---------------------------	-------

Connection

Connection cross-sect. flexible conductor	1,5 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 6mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------