



SRC04005

Bar/Cable-through Current Transformer BG 113 400/5A 5VA Class 1

Technical characteristics

Main electrical features

| | |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

Voltage

| | |
|--------------------------|------|
| Rated insulation voltage | 3 kV |
|--------------------------|------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 30 mm |
| Height of installed product | 70 mm |
| Width of installed product | 50 mm |
| Height of opening | 20 mm |

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 3.6 W |
|---------------------------|-------|

Connection

| | |
|--------------------|-------|
| Type of connection | screw |
|--------------------|-------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -40...40 °C |
|-----------------------|-------------|