



SRC06005

**Bar/Cable-through Current Transformer BG 113 600/5A 5VA Class 1**

**Technical characteristics**

**Specific identification attributes for Protection**

Filter Type product Plug-in current transformer

**Functions**

Accuracy class 1

**Power**

Power 5 VA

Total power loss under IN 5.50 W

**Dimensions**

Height 70 mm

Width 50 mm

Depth 30 mm

Height of opening 20 mm

Width of opening 29.50 mm

**Connectivity**

Type of connection Screw terminal

**Frequency**

Frequency 50 - 60 Hz

**Voltage**

Rated insulation voltage  $U_i$  3,000 V

**Use conditions**

Operating temperature -40 - 40 °C

Storage/transport temperature -40 - 40 °C

**Connection**

Cross-section flexible conductor 1.5 - 6 mm<sup>2</sup>

Cross-section rigid conductor 1.5 - 6 mm<sup>2</sup>

**Safety**

Ingress Protection (IP) class IP10

**Electric current**

Max. intensity of primary 600 A

Max. intensity of secondary 5 A

**Installation, mounting**

