



SRC06005

Bar/Cable-through Current Transformer BG 113 600/5A 5VA Class 1

Technical characteristics

Main electrical features

Frequency 50/60 Hz

Voltage

Rated insulation voltage 3 kV

Dimensions

Depth of installed product 30 mm

Height of installed product 70 mm

Width of installed product 50 mm

Height of opening 20 mm

Power

Total power loss under IN 5.5 W

Connection

Type of connection screw

Standards

European directive WEEE concerned

Use conditions

Operating temperature -40...40 °C