



SRC06005

Bar/Cable-through Current Transformer BG 113 600/5A 5VA Class 1

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	3 kV
--------------------------	------

Dimensions

Depth of installed product	30 mm
Height of installed product	70 mm
Width of installed product	50 mm
Height of opening	20 mm

Power

Total power loss under IN	5.5 W
---------------------------	-------

Connection

Type of connection	screw
--------------------	-------

Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------