



SRD08005

### Bar/Cable-through Current Transformer BG 613 800/5A 5VA Class 1

#### Technical characteristics

##### Main electrical features

Frequency	50/60 Hz
-----------	----------

##### Voltage

Rated insulation voltage	3 kV
--------------------------	------

##### Dimensions

Depth of installed product	30 mm
Height of installed product	108 mm
Width of installed product	85 mm
Height of opening	45 mm

##### Power

Total power loss under I <sub>N</sub>	6 W
---------------------------------------	-----

##### Connection

Type of connection	screw
--------------------	-------

##### Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------