



SRD10005

Bar/Cable-through Current Transformer BG 613 1000/5A 5VA Class 1

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	3 kV
--------------------------	------

Dimensions

Depth of installed product	30 mm
Height of installed product	108 mm
Width of installed product	85 mm
Height of opening	45 mm

Power

Total power loss under IN	8 W
---------------------------	-----

Connection

Connection cross-sect. flexible conductor	1,5 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 6mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------