



SRE20005

Bar/Cable-through Current Transformer BG 814 2000/5A 15VA Class 1

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	3 kV
--------------------------	------

Dimensions

Depth of installed product	40 mm
Height of installed product	122 mm
Width of installed product	100 mm
Height of opening	60 mm

Power

Total power loss under I _N	17.5 W
---------------------------------------	--------

Connection

Type of connection	screw
--------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP10
---------------------	------

Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------