



SRI03005

Bar/Cable-through Current Transformer BG 413 300/5A 5VA Class 1

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	3 kV
--------------------------	------

Dimensions

Depth of installed product	30 mm
Height of installed product	78 mm
Width of installed product	60 mm
Height of opening	28 mm

Power

Total power loss under I _N	3 W
---------------------------------------	-----

Connection

Type of connection	screw
--------------------	-------

Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------