



ST301



Bell transformer 4VA 230/8-12V

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	4000 V
--------------------------	--------

Dimensions

Depth of installed product	65 mm
Height of installed product	111 mm
Width of installed product	35 mm

Power

Power consumed	4 VA
Total power loss under IN	1.8 W

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²

Standards

Standard text	EN 61558-2-6
---------------	--------------

Use conditions

Operating temperature	-20...35 °C
-----------------------	-------------