



ST303



Bell transformer 8VA 230V 8-12V

Technical characteristics

Architecture

Fixing mode DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50 Hz

Voltage

Rated insulation voltage 4000 V

Dimensions

Depth of installed product 65 mm

Height of installed product 111 mm

Width of installed product 35 mm

Power

Power consumed 8 VA

Total power loss under IN 2.2 W

Standards

Standard text EN 61558-2-6

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -20...35 °C