



ST305



## Bell transformer 16VA 230V 8-12V

### Technical characteristics

#### Main electrical features

Rated operational voltage $U_e$	230 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	4000 V
--------------------------	--------

#### Dimensions

Depth of installed product	65 mm
Height of installed product	111 mm
Width of installed product	54 mm

#### Power

Power consumed	16 VA
Total power loss under IN	1.8 W

#### Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	4mm <sup>2</sup>
Connection cross-sect. rigid cable	6mm <sup>2</sup>

#### Standards

Standard text	EN 61558-2-6
---------------	--------------

#### Use conditions

Operating temperature	-20...35 °C
-----------------------	-------------