



ST312



Safety transformer 25VA 230V/12-24V

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	4000 V
--------------------------	--------

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Power consumed	25 VA
Total power loss under IN	1.8 W

Installation, mounting

Tightening torque	1,2Nm
Mounting type	din-Rail

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²

Standards

Standard text	EN 61558-2-6
European directive WEEE	concerned

Use conditions

Operating temperature	-20...35 °C
-----------------------	-------------