



ST312



## Safety transformer 25VA 230V/12-24V

### Technical characteristics

#### Architecture

Fixing mode DIN rail type O (symmetrical)

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50 Hz

#### Voltage

Rated insulation voltage 4000 V

#### Dimensions

Depth of installed product 58 mm

Height of installed product 85 mm

Width of installed product 70 mm

#### Power

Power consumed 25 VA

Total power loss under IN 1.8 W

#### Installation, mounting

Mounting type din-Rail

#### Standards

Standard text EN 61558-2-6

European directive WEEE concerned

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -20...35 °C