



ST315



Safety transformer 63VA 230V12-24V

Technical characteristics

Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	4000 V
--------------------------	--------

Dimensions

Depth of installed product	68 mm
Height of installed product	85 mm
Width of installed product	105 mm

Power

Power consumed	63 VA
----------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. rigid cable	6mm <sup>2</sup>
------------------------------------	------------------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...35 °C
-----------------------	-------------