



SU212



Bell 12V

Technical characteristics

Architecture

Fixing mode DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue 8 / 12 V

Type of supply voltage AC

Dimensions

Depth of installed product 65 mm

Height of installed product 80 mm

Width of installed product 18 mm

Power

Power consumed 5 VA

Total power loss under IN 5 W

Materials

Material polyamide

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -10...40 °C