



SU212



Bell 12V

Technical characteristics

Main electrical features

Rated operational voltage Ue	8 / 12 V
Type of supply voltage	AC

Dimensions

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

Power

Power consumed	5 VA
Total power loss under IN	5 W

Materials

Material	polyamide
----------	-----------

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²

Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------