



SU213



Bell 230V

Technical characteristics

Architecture

Fixing mode DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue 230 V

Type of supply voltage AC

Dimensions

Depth of installed product 65 mm

Height of installed product 80 mm

Width of installed product 18 mm

Power

Power consumed 6.5 VA

Total power loss under IN 6.5 W

Materials

Material polyamide

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -10...40 °C