



SU214



## Buzzer 12V

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue	8 / 12 V
Type of supply voltage	AC

#### Dimensions

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

#### Power

Power consumed	4 VA
Total power loss under IN	4 W

#### Materials

Material	polyamide
----------	-----------

#### Connection

Connection cross-sect. flexible conductor	4mm <sup>2</sup>
Connection cross-sect. rigid cable	6mm <sup>2</sup>

#### Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------