



SU214



## Buzzer 12V

### Technical characteristics

#### Architecture

Fixing mode DIN rail type O (symmetrical)

#### Main electrical features

Rated operational voltage Ue 8 / 12 V

Type of supply voltage AC

#### Dimensions

Depth of installed product 65 mm

Height of installed product 80 mm

Width of installed product 18 mm

#### Power

Power consumed 4 VA

Total power loss under IN 4 W

#### Materials

Material polyamide

#### Standards

European directive WEEE concerned

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...40 °C