



SU215



Buzzer 230V

Technical characteristics

Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC

Dimensions

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

Power

Power consumed	6.5 VA
Total power loss under IN	6.5 W

Materials

Material	polyamide
----------	-----------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------