



SU215



## Buzzer 230V

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC

#### Dimensions

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

#### Power

Power consumed	6.5 VA
Total power loss under IN	6.5 W

#### Materials

Material	polyamide
----------	-----------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------