



SVN122

## Red LED Indicator light 230VAC

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

#### Dimensions

Depth of installed product	62 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Power

Total power loss under IN	0.8 W
---------------------------	-------

#### Materials

Colour	red
--------	-----

#### Lighting control

Type of lamp	LED
--------------	-----

#### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 10mm <sup>2</sup>

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------