



SVN126

Green & red LED Double indicator light 230VAC

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

Dimensions

Depth of installed product	62 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	0.8 W
---------------------------	-------

Materials

Colour	red and green
--------	---------------

Lighting control

Type of lamp	LED
--------------	-----

Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	0,75 / 6mm ²
Connection cross-sect. rigid cable	0,75 / 10mm ²
Type of connection	with screw

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------