




SVN321



**Impulse 1NC Pushbutton**

**Technical characteristics**

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

**Dimensions**

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

**Power**

Total power loss under IN	0 W
---------------------------	-----

**Endurance**

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

**Materials**

Colour	not applicable
--------	----------------

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-20...50 °C
-----------------------	-------------