



SVN332



Latching 2NO Pushbutton

Technical characteristics

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	0 W
---------------------------	-----

Endurance

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

Materials

Colour	not applicable
--------	----------------

Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------