



SVN351



## Impulse 1NO/NC Pushbutton

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

#### Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Endurance

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

#### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

#### Connection

Type of connection	with screw
--------------------	------------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------