




SVN391



Impulse 1NO + 1NC Double Pushbutton

Technical characteristics

Main electrical features

| | |
|------------------------------|----------|
| Rated operational voltage Ue | 230 V |
| Frequency | 50/60 Hz |

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 250 V |
| Rated impulse withstand voltage | 4000 V |

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 66 mm |
| Height of installed product | 83 mm |
| Width of installed product | 17.5 mm |

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 0 W |
|---------------------------|-----|

Endurance

| | |
|--|-------|
| Electric endurance in number of cycles | 15000 |
| Number of mechanical operations | 15000 |

Materials

| | |
|--------|----------------|
| Colour | not applicable |
|--------|----------------|

Installation, mounting

| | |
|-------------------|-------|
| Tightening torque | 1,7Nm |
|-------------------|-------|

Connection

| | |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 0,75 / 6mm ² |
| Connection cross-sect. rigid cable | 0,75 / 10mm ² |
| Type of connection | with screw |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20...50 °C |
|-----------------------|-------------|